



VYGMS4W

**Group Metering Encl SA, 4, Wired**

**Technical Features**

**Installation, mounting**

Mounting on	DIN rail Surface mounting
-------------	------------------------------

**Electric current**

Breaking and opening capacity I <sub>dm</sub>	25 kA
---	-------

**Equipment**

Number of rows	2
Has mounting plate	No
Equipped with switch	MCCB
Number of switches	1
Type of busbar chassis	No chassis

**Capacity**

Number of modules	14
-------------------	----

**Dimensions**

Height	1050 mm
Width	440 mm
Depth	360 mm

**Materials**

Material	Steel
RAL code	7035
Colour	Light grey

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP23
Locking type	3-point lever

**Architecture**

Number of poles	14
-----------------	----