



16402079

Relay switch centre plate for hotel card, 1930/R.classic, p. white glossy

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	230 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Architecture

Control/operation element	Hotel card
Number of poles	1

Power

230 V incandescent and halogen lamp	1500 W
Fluorescent lamps in duo circuit	1500 W

Materials

Colour	Polar white
Surface finish	Glossy
Material	Metal Plastic
Treatment	Untreated
Transparent	No

Dimensions

Depth	60 mm
Built-in depth	32 mm
Built-in depth flush-mounted boxes	35 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	0
With feedback signal contact	No

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-5 - 50 °C
-----------------------	------------

Texts

Centre plates	With centre plate Ø 58 mm
Imprint	With imprint "Hotelcard"
Installation mode	With spreader claws
Lighting	For illumination
Switch mode	1-pole
Type of connection	With screw-in lift terminals

Suitable for

Serie 1930 / Serie Glas / Serie R.classic

Sustainability

RoHS conform	Yes
--------------	-----