



16402079

## Relay switch centre plate for hotel card, 1930/R.classic, p. white glossy

### Technical Features

#### Electric current

Switching current	10 A
Momentary contact current	10 A

#### Voltage

Rated voltage	230 V
---------------	-------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Architecture

Control/operation element	Hotel card
Number of poles	1

#### Power

230 V incandescent and halogen lamp	1500 W
Fluorescent lamps in duo circuit	1500 W

#### Materials

Colour	Polar white
Surface finish	Glossy
Material	Metal Plastic
Treatment	Untreated
Transparent	No

#### Dimensions

Depth	60 mm
Built-in depth	32 mm
Built-in depth flush-mounted boxes	35 mm

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Controls and indicators

Number of buttons	0
With feedback signal contact	No

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Accessories

Has labelling field	No
---------------------	----

#### Use conditions

Operating temperature	-5 - 50 °C
-----------------------	------------

#### Texts

Centre plates	With centre plate Ø 58 mm
Imprint	With imprint "Hotelcard"
Installation mode	With spreader claws
Lighting	For illumination
Switch mode	1-pole
Type of connection	With screw-in lift terminals

#### Suitable for

Serie 1930 / Serie Glas / Serie R.classic
---

#### Sustainability

RoHS conform	Yes
--------------	-----