



16402089



**Relay switch centre plate for hotel card, R.1/R.3, p. white glossy**

**Technical Features**

**Electric current**

Switching current	10 A
Momentary contact current	10 A

**Voltage**

Rated voltage	230 V
---------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Architecture**

Control/operation element	Hotel card
Number of poles	1

**Power**

230 V incandescent and halogen lamp	1500 W
Fluorescent lamps in duo circuit	1500 W

**Materials**

Colour	Polar white
Surface finish	Glossy
Material	Metal Plastic
Treatment	Untreated
Transparent	No

**Dimensions**

Height	69.50 mm
Width	69.50 mm
Depth	57.30 mm
Built-in depth	32 mm
Built-in depth flush-mounted boxes	35 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Controls and indicators**

Number of buttons	0
With feedback signal contact	No

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Accessories**

Has labelling field	No
---------------------	----

**Use conditions**

Operating temperature	-5 - 50 °C
-----------------------	------------

**Texts**

Imprint	With imprint "Hotelcard"
Installation mode	With spreader claws
Lighting	For illumination
Switch mode	1-pole
Type of connection	With screw-in lift terminals

**Suitable for**

R.x	
-----	--

---

**Sustainability**

---

RoHS conform

Yes