



60060

Universal load shedder 3 rotary channels, 3 modules

Technical Features

Frequency

Frequency 50 - 50 Hz

Capacity

Number of modules 3

Use conditions

Operating temperature 0 - +50 °C

Storage/transport temperature -20 - +60 °C

Dimensions

Height 80 mm

Width 52 mm

Depth 60 mm

Illustrations | Drawings

