



75910001

Power supply 24 V~ 1A

Technical Features

Capacity

Number of modules

4

Electric current

Output current

1000 mA

Connectivity

With bus system KNX radio

No

Voltage

Operating voltage

230 - 230 V

Output voltage

24 - 24 V

Use conditions

Operating temperature

-5 - 45 °C

Frequency

Frequency

50 - 60 Hz

Texts

Fuse Short-circuit-proof and overload-proof (thermal protection)

Type of connection With screw terminals

Sustainability

REACH-SVHC free

Yes

RoHS conform

Yes