



EC700

Pulses concentrator

Technical Features

Electric current

Number of entry circuits	7
--------------------------	---

Dimensions

Height	90 mm
Width	67 mm
Depth	50 mm

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Installation, mounting

Mounting on	DIN rail
-------------	----------

Use conditions

Operating temperature	-10 - 55 °C
-----------------------	-------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes