



260205



**230 V USB charging socket outlet, 2gang, 3.0A, angular supporting ring, anthr.**

**Technical Features**

**Connectivity**

|                         |                |
|-------------------------|----------------|
| Type of connection      | Screw terminal |
| Connector/plug type USB | A              |

**Dimensions**

|                                    |       |
|------------------------------------|-------|
| Built-in depth                     | 32 mm |
| Built-in depth flush-mounted boxes | 34 mm |

**Equipment**

|                   |   |
|-------------------|---|
| Number of outputs | 2 |
|-------------------|---|

**Accessories**

|                     |    |
|---------------------|----|
| Has labelling field | No |
| With miniature fuse | No |

**Materials**

|                |            |
|----------------|------------|
| Colour         | Anthracite |
| RAL code       | 7021       |
| Surface finish | Matt       |

**Power**

|                           |        |
|---------------------------|--------|
| Output power              | 15 W   |
| Power consumption standby | 0.15 W |

**Voltage**

|                |             |
|----------------|-------------|
| Input voltage  | 230 - 230 V |
| Output voltage | 5 - 5 V     |

**Electric current**

|                |         |
|----------------|---------|
| Rated current  | 0.20 A  |
| Output current | 3000 mA |

**Texts**

|                    |  |
|--------------------|--|
| Connectors jacks   | With 2 USB sockets type A                          |
| Fuse               | Short-circuit and overload-proof (electronic fuse) |
| Type of connection | With screw terminals                               |
| Protection         | Without enhanced contact protection                |

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |