



928912506

Rotary Potentiometer 1-10V with Setting Knob and Frame, Soft Lock, Grey Glossy

Technical Features

Voltage

Operating voltage 230 - 230 V

Frequency

Frequency 50 - 60 Hz

Connectivity

Dimming DALI No

Dimensions

Diameter axis 4 mm

Built-in depth 22 mm

Height 59.50 mm

Width 59.50 mm

Depth 58 mm

Electric current

Control current 50 - 50 mA

Switching current 6 A

Materials

Colour Grey

Texts

Lighting E.g. for fluorescent lamps and LV halogen lamps

Type of connection With screw terminals

Fuse Short-circuit and overload-proof (fine-wire fuse)
With spare fuse

Suitable for

integro

Sustainability

REACH-SVHC free Yes

RoHS conform Yes