



928912501



Rotary Potentiometer 1-10V with Setting Knob and Frame, Soft Lock, Brown Matt

Technical Features

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Connectivity

Dimming DALI	No
--------------	----

Dimensions

Diameter axis	4 mm
Built-in depth	22 mm
Height	59.50 mm
Width	59.50 mm
Depth	58 mm

Electric current

Control current	50 - 50 mA
Switching current	6 A

Materials

Colour	Brown
--------	-------

Texts

Lighting	E.g. for fluorescent lamps and LV halogen lamps
Type of connection	With screw terminals
Fuse	Short-circuit and overload-proof (fine-wire fuse) With spare fuse

Suitable for

integro	
---------	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes