



296110

Universal rotary dimmer comfort (R, L, C, LED), soft-lock, light control

Technical Features

Voltage

Operating voltage 230 - 230 V

Frequency

Frequency 50 - 60 Hz

Materials

Material Metal Plastic

Dimensions

Diameter axis 4 mm

Built-in depth 24 mm

Height 71 mm

Width 71 mm

Depth 43 mm

Architecture

Control/operation element Push & rotative switch

Lighting

Dimmable 230 V LED lamp 3 - 100 W

Texts

Dimming principle Phase cut-on, cut-off or LED phase cut-on according to load type, self-learning

Fuse Short-circuit and overload-proof (electronic fuse)

Voltage Voltage test possible without dismantling

Installation mode With spreader claws

Type of connection With screw terminals

Extension unit input With extension unit input for push-button (NO contact) With single-surface operation
With input for extension units insert for universal rotary dimmer

Operation and control No Bluetooth interface

Sustainability

REACH-SVHC free Yes

RoHS conform Yes