



VE312L

Enclosure, vector, IP5x, 36Modules, Austria

**Technical Features**

**Voltage**

Nominal voltage 400 - 400 V

**Installation, mounting**

Suitable for outdoor usage No

Mounting on Surface mounting

**Electric current**

Rated current 63 A

**Equipment**

Number of rails 3

Number of rows 3

Number of section in width 1

With lock No

Has neutral terminal block No

**Capacity**

Number of modules 36

**Functions**

With conduit inlets Yes

**Dimensions**

Height 552 mm

Width 310 mm

Depth 151 mm

**Cover, door**

Number of cabinet doors 1

Number of locks 0

**Dimensions**

Number of width units 12

**Cover, door**

Door/cover is transparent Yes

**Connection**

Number of conduit inlets 12

**Materials**

Material Polystyrene (PS)

RAL code 7035

Colour Light grey

**Equipment**

Has earthing terminal block No

Has mounting plate No

**Materials**

Ultraviolet-resistant No

**Safety**

Protection class Isolation class II

Impact resistance IK IK08

Ingress Protection (IP) class IP65

Locking type Snap on lock  
Without lock

Glow wire test 750 °C