



VE312L

Enclosure, vector, IP5x, 36Modules, Austria

Technical Features

Voltage

Nominal voltage 400 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Surface mounting

Electric current

Rated current 63 A

Equipment

Number of rails 3

Number of rows 3

Number of section in width 1

With lock No

Has neutral terminal block No

Capacity

Number of modules 36

Functions

With conduit inlets Yes

Dimensions

Height 552 mm

Width 310 mm

Depth 151 mm

Cover, door

Number of cabinet doors 1

Number of locks 0

Dimensions

Number of width units 12

Cover, door

Door/cover is transparent Yes

Connection

Number of conduit inlets 12

Materials

Material Polystyrene (PS)

RAL code 7035

Colour Light grey

Equipment

Has earthing terminal block No

Has mounting plate No

Materials

Ultraviolet-resistant No

Safety

Protection class Isolation class II

Impact resistance IK IK08

Ingress Protection (IP) class IP65

Locking type Snap on lock
Without lock

Glow wire test 750 °C