



JG34BS

125A TPN NON-AUTO MCCB

Technical Features

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Functions

| | |
|------------------------|-----|
| Overvoltage protection | Yes |
|------------------------|-----|

Electric current

| | |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

Dimensions

| | |
|--------|--------|
| Depth | 106 mm |
| Height | 420 mm |
| Width | 200 mm |

Cover, door

| | |
|---------------------------|----|
| Interlockable | No |
| Door/cover is transparent | No |

Materials

| | |
|----------|------------|
| RAL code | 7035 |
| Colour | Light grey |
| Material | Steel |

Connection

| | |
|-----------------------------|---|
| Number of accessible phases | 3 |
|-----------------------------|---|

Scope of delivery

| | |
|-----------------------------|---|
| Number of RCCB in enclosure | 0 |
|-----------------------------|---|

Equipment

| | |
|--------------------|----|
| With socket outlet | No |
|--------------------|----|

Safety

| | |
|---|---------------------|
| Ingress Protection (IP) class | IP3X |
| Protection class | Isolation class III |
| Number of earth leakage switches 300 mA | 0 |