



VE318AK

**Enclosure,vector,IP55,3x18Modules**

**Technical Features**

**Voltage**

Nominal voltage	400 - 400 V
-----------------	-------------

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	63 A
---------------	------

**Equipment**

Number of rails	3
Number of rows	3
Number of section in width	1
With lock	No

**Capacity**

Number of modules	54
-------------------	----

**Functions**

With conduit inlets	Yes
---------------------	-----

**Dimensions**

Height	602 mm
Width	418 mm
Depth	151 mm

**Cover, door**

Number of cabinet doors	1
Number of locks	0

**Dimensions**

Number of width units	18
-----------------------	----

**Cover, door**

Door/cover is transparent	Yes
---------------------------	-----

**Connection**

Number of conduit inlets	15
--------------------------	----

**Materials**

Material	Polystyrene (PS)
RAL code	7035
Colour	Light grey

**Equipment**

Has mounting plate	No
--------------------	----

**Materials**

Ultraviolet-resistant	No
-----------------------	----

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP65
Locking type	Snap on lock Without lock
Glow wire test	750 °C

**Sustainability**

RoHS conform	Yes
--------------	-----