



WGCR121P

10A 2G press round switch

Technical Features

Electric current

Switching current	10 A
-------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Double push button
---------------------------	--------------------

Materials

Colour	White
--------	-------

Surface finish	Glossy
----------------	--------

Material	Polycarbonate (PC)
----------	--------------------

Treatment	Untreated
-----------	-----------

Transparent	No
-------------	----

Dimensions

Height	86 mm
--------	-------

Width	86 mm
-------	-------

Depth	25 mm
-------	-------

Built-in depth flush-mounted boxes	35 mm
------------------------------------	-------

Controls and indicators

Number of buttons	2
-------------------	---

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Accessories

Has labelling field	No
---------------------	----

Suitable for

shark	
-------	--

Sustainability

RoHS conform	Yes
--------------	-----