



WGML131PKB

10A 3G press switch;kb

Technical Features

Electric current

| | |
|-------------------|------|
| Switching current | 10 A |
|-------------------|------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Triple rocker |
|---------------------------|---------------|

Materials

| | |
|----------------|--------------------|
| Colour | Knight black |
| Surface finish | Matt |
| Material | Polycarbonate (PC) |
| Treatment | Varnished |
| Transparent | No |

Dimensions

| | |
|------------------------------------|-------|
| Height | 86 mm |
| Width | 86 mm |
| Depth | 25 mm |
| Built-in depth flush-mounted boxes | 35 mm |

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 3 |
|-------------------|---|

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Suitable for

| | |
|-------|--|
| shark | |
|-------|--|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|