



JKD11111

Dual Metered, Dual Row 22way 100A MID Pulsed, Modbus

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Architecture

Number of poles	2
-----------------	---

Functions

Has protection main switch	Yes
----------------------------	-----

Capacity

Number of modules	22
-------------------	----

Electric current

Rated current	100 A
---------------	-------

Dimensions

Depth	125 mm
Height	472 mm
Width	398 mm

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

RAL code	7035 9010
Colour	Light grey
Material	Steel

Connection

Number of accessible phases	2
-----------------------------	---

Scope of delivery

Number of RCCB in enclosure	0
-----------------------------	---

Equipment

Number of rows	2
With energy meter	Yes
With socket outlet	No

Safety

Ingress Protection (IP) class	IP2XC
-------------------------------	-------