



SVN342

Latching 2NC Pushbutton

Technical Features

Equipment

Number of INV contacts	0
Number of NC contacts	2
Number of NO contacts	0
With signal lamp	No

Electric current

Momentary contact current	16 A
Rated current	16 A

Capacity

Number of modules	1
-------------------	---

Dimensions

Height	83 mm
Width	17.50 mm
Depth	66 mm

Voltage

Rated insulation voltage $U_i$	250 V
Rated operational voltage $U_e$	230 - 230 V

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

