



HBT160H

RCD add on P250 4P 160A Idn adj

Technical Features

Electric current

Rated current I _N	160 A
Rated residual operating current I _{Δn}	30 mA
	100 mA
	300 mA
	1000 mA
	3000 mA
	6000 mA

Architecture

Number of poles	4
-----------------	---

Safety

Residual current type	A
-----------------------	---

Voltage

Rated insulation voltage U _i	500 V
Rated impulse withstand voltage U _{imp}	6000 V

Connection

Cross-section of input and output with screws, for massive conductors	35 - 185 mm ²
Cross-section of input and output with screws, for flexible conductors	35 - 150 mm ²

Sustainability

RoHS conform	Yes
--------------	-----