



2909

Rotary dimmer (R, LED), light control

Technical Features

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Material	Metal Plastic
----------	------------------

Dimensions

Diameter axis	4 mm
Built-in depth	31 mm
Height	71 mm
Width	71 mm
Depth	50 mm

Architecture

Control/operation element	Rotative
---------------------------	----------

Power

Power consumption standby	0.20 W
---------------------------	--------

Lighting

Dimmable 230 V LED lamp	3 - 40 W
-------------------------	----------

Texts

Dimming principle	Phase cut-on
Fuse	Short-circuit and overload-proof (fine-wire fuse)
Installation mode	With spreader claws
Type of connection	With screw terminals
Operation and control	No Bluetooth interface

Equipment

Substation input	No
------------------	----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes