



2998



Rotary potentiometer DALI with power supply, TW, soft-lock, light control

Technical Features

Frequency

Frequency 50 - 60 Hz

Lighting

Colour temperature 2000 - 10000 K

Connectivity

Dimming DALI Yes

Dimensions

Diameter axis 4 mm

Built-in depth 31 mm

Height 71 mm

Width 71 mm

Depth 50 mm

Electric current

Control current 52 - 52 mA

Texts

Lighting E.g. fluorescent lamps, NV-halogen lamps and LED

Type of connection With screw terminals

Fuse Short-circuit and overload-proof (electronic fuse)

Suitable for

K.x / Q.x / R.x / S.x/B.x

Sustainability

REACH-SVHC free Yes

RoHS conform Yes