



2997



**Rotary potentiometer DALI, Tunable white, soft-lock, light control**

**Technical Features**

**Frequency**

Frequency 50 - 60 Hz

**Lighting**

Colour temperature 2000 - 10000 K

**Connectivity**

Dimming DALI Yes

**Dimensions**

Diameter axis 4 mm

Built-in depth 31 mm

Height 71 mm

Width 71 mm

Depth 50 mm

**Texts**

Lighting E.g. fluorescent lamps, NV-halogen lamps and LED

Type of connection With screw terminals

Fuse Short-circuit and overload-proof (electronic fuse)

**Suitable for**

K.x / Q.x / R.x / S.x/B.x

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes