



FWB74GS

FWB encl. univers,surface mount.,IP44,classII,w. transp.door;1100x1050x161mm,QC

Technical Features

Installation, mounting

| | |
|----------------------------|------------------|
| Suitable for outdoor usage | No |
| Mounting on | Surface mounting |

Electric current

| | |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

Equipment

| | |
|----------------------------|-----|
| Number of rails | 28 |
| Number of rows | 28 |
| Number of section in width | 4 |
| With lock | No |
| Has neutral terminal block | Yes |

Capacity

| | |
|-------------------|-----|
| Number of modules | 336 |
|-------------------|-----|

Functions

| | |
|---------------------|-----|
| With conduit inlets | Yes |
|---------------------|-----|

Dimensions

| | |
|--------|---------|
| Height | 1100 mm |
| Width | 1050 mm |
| Depth | 165 mm |

Cover, door

| | |
|-------------------------|---|
| Number of cabinet doors | 2 |
| Number of locks | 1 |

Dimensions

| | |
|-----------------------|----|
| Number of width units | 48 |
|-----------------------|----|

Cover, door

| | |
|---------------------------|-------|
| Type of handle | Latch |
| Door/cover is transparent | Yes |

Connection

| | |
|--------------------------|----|
| Number of conduit inlets | 16 |
|--------------------------|----|

Materials

| | |
|----------|------------|
| Material | Steel |
| RAL code | 9010 |
| Colour | Pure white |

Equipment

| | |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate | No |

Safety

| | |
|-------------------------------|--------------------|
| Protection class | Isolation class II |
| Impact resistance IK | IK07 |
| Ingress Protection (IP) class | IP44 |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|