



2973

**Universal rotary dimmer (R, L, C, LED), light control**

**Technical Features**

**Voltage**

Operating voltage 230 - 230 V

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Material Metal Plastic

**Dimensions**

Diameter axis 4 mm

Built-in depth 24 mm

Height 71 mm

Width 71 mm

Depth 43 mm

**Architecture**

Control/operation element Push & rotative switch

**Lighting**

Dimmable 230 V LED lamp 3 - 60 W

**Texts**

Dimming principle Phase cut-on or cut-off according to load type, self-learning

Fuse Short-circuit and overload-proof (electronic fuse)

Voltage Voltage test possible without dismantling

Installation mode With spreader claws

Type of connection With screw terminals

Operation and control No Bluetooth interface

**Equipment**

Substation input No

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes