

Load Break Switch Disconnecter h3 x160 4P 160A CTC

Technical Features

Electric current

Rated current	160 A
---------------	-------

Architecture

Number of poles	4
-----------------	---

Control/operation element	Toggle
---------------------------	--------

Connection

Cross-section rigid conductor	4 - 95 mm <sup>2</sup>
-------------------------------	------------------------

Cross-section flexible conductor	4 - 70 mm <sup>2</sup>
----------------------------------	------------------------

Voltage

Rated insulation voltage U <sub>i</sub>	690 V
---	-------

Rated impulse withstand voltage U <sub>imp</sub>	8000 V
--	--------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Functions

Trip unit	Switch
-----------	--------

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----