

Load Break Switch Disconnecter h3 x160 4P 160A CTC

Technical Features

Electric current	
Rated current	160 A
Architecture	
Number of poles	4
Control/operation element	Toggle
Connection	
Cross-section rigid conductor	4 - 95 mm ²
Cross-section flexible conductor	4 - 70 mm ²
Voltage	
Rated insulation voltage Ui	690 V
Rated impulse withstand voltage Uimp	8000 V
Frequency	
Frequency	50 - 60 Hz
Functions	
Trip unit	Switch
Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes