



WRPS22PSB

10AX 2 Gang 2 Way Wall Switch Polished Steel Black Insert

Technical Features

Electric current

| | |
|-------------------|------|
| Switching current | 10 A |
|-------------------|------|

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Materials

| | |
|--------|--------|
| Colour | Silver |
|--------|--------|

| | |
|----------------|--------|
| Surface finish | Glossy |
|----------------|--------|

| | |
|----------|-----------------|
| Material | Stainless steel |
|----------|-----------------|

Identification

| | |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 2 |
|-------------------|---|

Dimensions

| | |
|------------|------------|
| Dimensions | 86 x 86 mm |
|------------|------------|

| | |
|----------------|----------|
| Built-in depth | 11.20 mm |
|----------------|----------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Double rocker |
|---------------------------|---------------|

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Texts

| | |
|-------------------|--|
| Installation mode | For flush-mounted and hollow wall mounting |
|-------------------|--|

| | |
|----------|--|
| Lighting | Without lighting (cannot be illuminated) |
|----------|--|

| | |
|-------------|-------|
| Switch mode | 2-way |
|-------------|-------|

Sustainability

| | |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|