



SVN331

Impulse 2NO Pushbutton

Technical Features

Equipment

|                        |    |
|------------------------|----|
| Number of INV contacts | 0  |
| Number of NC contacts  | 0  |
| Number of NO contacts  | 2  |
| With signal lamp       | No |

Electric current

|                           |      |
|---------------------------|------|
| Momentary contact current | 16 A |
| Rated current             | 16 A |

Capacity

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Dimensions

|        |          |
|--------|----------|
| Height | 83 mm    |
| Width  | 17.50 mm |
| Depth  | 66 mm    |

Voltage

|                              |             |
|------------------------------|-------------|
| Rated insulation voltage Ui  | 250 V       |
| Rated operational voltage Ue | 230 - 230 V |

Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |

Illustrations | Drawings

