



SVN331

### Impulse 2NO Pushbutton

#### Technical Features

##### Equipment

Number of INV contacts	0
Number of NC contacts	0
Number of NO contacts	2
With signal lamp	No

##### Electric current

Momentary contact current	16 A
Rated current	16 A

##### Capacity

Number of modules	1
-------------------	---

##### Dimensions

Height	83 mm
Width	17.50 mm
Depth	66 mm

##### Voltage

Rated insulation voltage Ui	250 V
Rated operational voltage Ue	230 - 230 V

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes

### Illustrations | Drawings

