



TRM693G



1 FLUSH MOUNTED OUTPUT 3A 230V + 2 INPUTS MAINS POWERED KNX RF

Technical Features

Connectivity

Radio protocol KNX Radio

Settings

Supported configuration mode ETS
easy
quicklink

Connectivity

Receiver category 2
With bus system KNX No
With bus system KNX radio Yes

Dimensions

Dimensions 40 x 40 mm
Height 40 mm
Width 40 mm
Depth 20 mm
Built-in depth 40 mm

Electric current

Rated current 3 A

Materials

Colour Light grey

Equipment

Radio frequency bidirectional Yes
With switch for manual switch Yes

Frequency

Frequency 50 - 50 Hz
Radio reception frequency 868.30 - 868.30 MHz

Power

Output power 690 W
230 V incandescent and halogen lamp 500 W

Voltage

Operating voltage 230 - 230 V
Rated operational voltage U_e 230 - 230 V
System supply voltage 230 V AC

Safety

Ingress Protection (IP) class IP20

Use conditions

Operating temperature -10 - 50 °C

Connection

Cross-section rigid conductor 0.5 - 2.5 mm²
Cross-section flexible conductor 0.5 - 1.5 mm²

Texts

Function Easy additional functions: +6 scenes
Repeat function can be activated to increase the radio range
Reset function (to factory setting)
Installation mode For installation behind flush-mounted inserts
Type of connection With screw-in lift terminals