



TRM691E



1 FLUSH MOUNTED DIMMER 200W 2 WIRES + 2 INPUTS KNX RF

Technical Features

Voltage

System supply voltage	230 V AC
-----------------------	----------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Use conditions

Operating temperature	-15 - 45 °C
-----------------------	-------------

Connection

Cross-section flexible conductor	0.5 - 1.5 mm ²
Cross-section rigid conductor	0.5 - 2.5 mm ²

Equipment

Number of outputs	1
Type of dimmer	Universal

Capacity

Number of modules	0
-------------------	---

Power

Power incandescent lamp	10 - 200 W
Power of variator	200 - 200 W

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Lighting

Dimmable 230 V LED lamp	3 - 50 W
-------------------------	----------

Settings

Supported configuration mode	quicklink
------------------------------	-----------

Texts

Fuse	Short-circuit and overload-proof (electronic fuse)
Dimming principle	Phase cut-on or cut-off according to load type, self-learning
Function	Easy additional functions: +6 scenes Reset function (to factory setting)
Type of connection	With screw-in lift terminals