



VYGMS6W

Group Metering Encl SA, 6, Wired

Technical Features

Installation, mounting

Mounting on	DIN rail Surface mounting
-------------	------------------------------

Electric current

Breaking and opening capacity I _{dm}	25 kA
---	-------

Equipment

Number of rows	2
Has mounting plate	No
Equipped with switch	MCCB
Number of switches	1
Type of busbar chassis	No chassis

Capacity

Number of modules	20
-------------------	----

Dimensions

Height	1050 mm
Width	625 mm
Depth	360 mm

Materials

Material	Steel
RAL code	7035
Colour	Light grey

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP23
Locking type	3-point lever

Architecture

Number of poles	20
-----------------	----

Sustainability

RoHS conform	Yes
--------------	-----