



TRM690G



## 1 FLUSH MOUNTED OUTPUT 200W, 2 WIRES + 2 INPUTS KNX RF

### Technical Features

#### Connectivity

Radio protocol	KNX Radio
----------------	-----------

#### Settings

Supported configuration mode	ETS easy quicklink
------------------------------	--------------------------

#### Connectivity

Receiver category	2
With bus system KNX	No
With bus system KNX radio	Yes

#### Dimensions

Dimensions	18 x 40 mm
Height	18 mm
Width	40 mm
Depth	18 mm
Built-in depth	40 mm

#### Electric current

Rated current	0.85 A
---------------	--------

#### Materials

Colour	Light grey
--------	------------

#### Equipment

Radio frequency bidirectional	Yes
With switch for manual switch	Yes

#### Frequency

Frequency	50 - 50 Hz
Radio reception frequency	868.30 - 868.30 MHz

#### Power

Output power	200 W
--------------	-------

#### Voltage

Operating voltage	230 - 230 V
Rated operational voltage Ue	230 - 230 V
System supply voltage	230 V AC

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Use conditions

Operating temperature	-15 - 45 °C
-----------------------	-------------

#### Connection

Cross-section rigid conductor	0.5 - 2.5 mm <sup>2</sup>
Cross-section flexible conductor	0.5 - 1.5 mm <sup>2</sup>

#### Texts

Function	Easy additional functions: +6 scenes Reset function (to factory setting)
----------	---

Installation mode	For installation behind flush-mounted inserts
-------------------	---

Type of connection	With screw-in lift terminals
--------------------	------------------------------