




75141830



IP20

KNX glass sensor 1gang comf, intg bus coupl. unit, KNX-TS sensor, glass p.white

Technical Features

Installation, mounting

Mounting on Flush mounting

Use conditions

Operating temperature -5 - 45 °C

Functions

With room temperature controller Yes

Power

Current consumption 12.50 mA

Dimensions

Built-in depth 24.20 mm

Built-in depth flush-mounted boxes 27 mm

Height 160 mm

Width 86 mm

Depth 37.70 mm

Equipment

Number of actuation points 2

Controls and indicators

With LED indication Yes

Materials

Colour Polar white

RAL code 9010

Material Glass

Surface finish Glossy

Accessories

Has labelling field No

Screen

With display No

Texts

Function For switch, push-button, dimmer and shutter functions
Blocking function for sensor surface e.g. for cleaning the glass surface

Installation mode For vertical mounting

Temperature Additional connection for external temperature sensor
Integrated temperature sensor for operation as controller extension unit
Temperature measurement via internal Temperature sensor or external communication object

Sustainability

REACH-SVHC free Yes

RoHS conform Yes