

Enclosed MCCB 3-Pole 160A , 25kA (Adjustable 100A - 128A - 160A)

Technical Features

Installation, mounting

Mounting on Surface mounting

Functions

Overvoltage protection Yes

Electric current

Rated current 160 A

Dimensions

Depth 135 mm

Height 660 mm

Width 260 mm

Cover, door

Interlockable No

Door/cover is transparent No

Materials

RAL code 7035

Colour Light grey

Material Steel

Connection

Number of accessible phases 3

Scope of delivery

Number of RCCB in enclosure 0

Equipment

With socket outlet No

Safety

Ingress Protection (IP) class IP3X

Protection class Isolation class III