



WMS82

### 13A 2 Gang Unswitched Socket Dual Earth

#### Technical Features

##### Voltage

Rated voltage	250 V
---------------	-------

##### Electric current

Rated current	13 A
---------------	------

##### Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

##### Dimensions

Height	86 mm
Width	146 mm
Depth	26.20 mm

##### Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

##### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

##### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	0
-------------------	---

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Functions

With orientation lighting	No
With function lighting	No

##### Identification

With imprint	No
--------------	----

##### Texts

Cover	Full cover plate
Wiring	With double earth connection
Protection	Enhanced contact protection

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes