



WMGKS

20A Double Pole Key Switch

Technical Features

Electric current

| | |
|---------------------------|------|
| Momentary contact current | 10 A |
|---------------------------|------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Single rocker |
| Number of poles | 2 |

Materials

| | |
|----------------|-------------------|
| Colour | White |
| Surface finish | Glossy |
| Material | Urea formaldehyde |
| Treatment | Untreated |
| Transparent | No |

Dimensions

| | |
|--------|-------|
| Height | 60 mm |
| Width | 25 mm |
| Depth | 24 mm |

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Controls and indicators

| | |
|------------------------------|----|
| Number of buttons | 0 |
| With feedback signal contact | No |

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Texts

| | |
|----------|-------------------|
| Imprint | Without imprint |
| Lighting | Without neon lamp |

Suitable for

| | |
|----------|--|
| sollysta | |
|----------|--|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |