



WMGKS

**20A Double Pole Key Switch**

**Technical Features**

**Electric current**

Momentary contact current	10 A
---------------------------	------

**Voltage**

Rated voltage	250 V
---------------	-------

**Architecture**

Control/operation element	Single rocker
Number of poles	2

**Materials**

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated
Transparent	No

**Dimensions**

Height	60 mm
Width	25 mm
Depth	24 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Controls and indicators**

Number of buttons	0
With feedback signal contact	No

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Accessories**

Has labelling field	No
---------------------	----

**Texts**

Imprint	Without imprint
Lighting	Without neon lamp

**Suitable for**

sollysta	
----------	--

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes