



FR14E2

Steel enclosure, Univers, IP55, CL1, 1700x1050x275 mm, plinth H200 mm

### Technical Features

#### Dimensions

Height	1900 mm
Width	1050 mm
Depth	275 mm
Thickness of sidewall	1.50 mm

#### Safety

Ingress Protection (IP) class	IP55
Protection class	Isolation class I
Locking type	Without lock
Impact resistance IK	IK10

#### Equipment

Number of section in width	4
Number of flange plate openings	8

#### Installation, mounting

Mounting on	Floor mounting
Suitable for outdoor usage	No

#### Materials

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel

#### Equipment

Number of rows	11
----------------	----

#### Materials

Surface finish	Matt
----------------	------

#### Cover, door

Number of cabinet doors	2
Number of locks	1
Door/cover is transparent	No

#### Electric current

Rated current	800 A
---------------	-------

#### Voltage

Nominal voltage	690 - 690 V
-----------------	-------------

#### Sustainability

RoHS conform	Yes
--------------	-----