



FR14E1

Steel enclosure, Unipers, IP55, CL1, 1700x1050x275 mm, plinth H100 mm

Technical Features

Dimensions

| | |
|-----------------------|---------|
| Height | 1800 mm |
| Width | 1050 mm |
| Depth | 275 mm |
| Thickness of sidewall | 1.50 mm |

Safety

| | |
|-------------------------------|-------------------|
| Ingress Protection (IP) class | IP55 |
| Protection class | Isolation class I |
| Locking type | Without lock |
| Impact resistance IK | IK10 |

Equipment

| | |
|---------------------------------|---|
| Number of section in width | 4 |
| Number of flange plate openings | 8 |

Installation, mounting

| | |
|----------------------------|----------------|
| Mounting on | Floor mounting |
| Suitable for outdoor usage | No |

Materials

| | |
|-----------|---------------|
| Colour | Light grey |
| RAL code | 7035 |
| Treatment | Powder coated |
| Material | Steel |

Equipment

| | |
|----------------|----|
| Number of rows | 11 |
|----------------|----|

Materials

| | |
|----------------|------|
| Surface finish | Matt |
|----------------|------|

Cover, door

| | |
|---------------------------|----|
| Number of cabinet doors | 2 |
| Number of locks | 1 |
| Door/cover is transparent | No |

Electric current

| | |
|---------------|-------|
| Rated current | 800 A |
|---------------|-------|

Voltage

| | |
|-----------------|-------------|
| Nominal voltage | 690 - 690 V |
|-----------------|-------------|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|