



WFSS81PSB

13A 1 Gang Double Pole Switched Socket Polished Steel Black Insert

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Rated current	13 A
---------------	------

Materials

Colour	Silver
Surface finish	Glossy
Material	Stainless steel

Dimensions

Height	86 mm
Width	86 mm
Depth	25.80 mm

Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	0
-------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	Without imprint
Cover	Full cover plate
Wiring	With earth connection
Protection	Enhanced contact protection

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes