



**FLUSH CONSUMER UNIT 8 WAY W/S FOR AI SW**

**Technical Features**

**Voltage**

Nominal voltage	230 - 415 V
-----------------	-------------

**Installation, mounting**

Suitable for outdoor usage	No
----------------------------	----

**Equipment**

Number of rails	1
Number of rows	1

**Capacity**

Number of modules	8
-------------------	---

**Dimensions**

Height	251 mm
Width	306 mm
Depth	20 mm
Built-in width	280 mm

**Cover, door**

Number of cabinet doors	1
-------------------------	---

**Dimensions**

Built-in depth	71 mm
----------------	-------

**Cover, door**

Number of locks	0
-----------------	---

**Dimensions**

Number of width units	8
-----------------------	---

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Connection**

Number of conduit inlets	12
--------------------------	----

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Materials**

Material	Steel
RAL code	9002
Colour	Grey white

**Equipment**

Has mounting plate	No
--------------------	----

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP40
Locking type	Without lock

**Sustainability**

RECh-SVHC free	Yes
----------------	-----