



JHF80408BG

800A 12 Way Panelboard 4*250A + 8*125A Glazed Door

Technical Features

Connection

| | |
|-----------------------------|---|
| Number of accessible phases | 3 |
|-----------------------------|---|

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Electric current

| | |
|---------------|-------|
| Rated current | 800 A |
|---------------|-------|

Equipment

| | |
|----------------------------|-----|
| With lock | Yes |
| Has neutral terminal block | Yes |

Capacity

| | |
|-------------------|----|
| Number of modules | 12 |
|-------------------|----|

Dimensions

| | |
|--------|---------|
| Height | 2050 mm |
| Width | 900 mm |
| Depth | 220 mm |

Cover, door

| | |
|---------------------------|-----|
| Number of cabinet doors | 1 |
| Door/cover is transparent | Yes |

Materials

| | |
|----------|------------|
| Material | Steel |
| RAL code | 7035 |
| Colour | Light grey |

Equipment

| | |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
|-----------------------------|-----|

Safety

| | |
|-------------------------------|-------------------|
| Protection class | Isolation class I |
| Ingress Protection (IP) class | IP2XC |
| Locking type | Quarter turn lock |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|