



JKD114

**Dual Metered 14way 100A Config MID Pulsed, Modbus**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Architecture**

Number of poles	2
-----------------	---

**Functions**

Has protection main switch	Yes
----------------------------	-----

**Capacity**

Number of modules	14
-------------------	----

**Electric current**

Rated current	100 A
---------------	-------

**Dimensions**

Depth	125 mm
-------	--------

Height	236 mm
--------	--------

Width	505 mm
-------	--------

**Cover, door**

Interlockable	No
---------------	----

Door/cover is transparent	No
---------------------------	----

**Materials**

RAL code	7035
----------	------

Colour	Light grey
--------	------------

Material	Steel
----------	-------

**Connection**

Number of accessible phases	2
-----------------------------	---

**Scope of delivery**

Number of RCCB in enclosure	0
-----------------------------	---

**Equipment**

Number of rows	1
----------------	---

With energy meter	Yes
-------------------	-----

**Safety**

Ingress Protection (IP) class	IP2XC
-------------------------------	-------

Protection class	Isolation class I
------------------	-------------------