



SR400

### Current transformer 400 / 5A

#### Technical Features

##### Functions

Accuracy class

1

##### Power

Power

12 VA

Total power loss under IN

0 W

#### Dimensions

Diameter of opening

35 mm

Height

70 mm

Width

77 mm

Depth

75 mm

Height of opening

40 mm

Width of opening

10 mm

#### Connectivity

Type of connection

Screw terminal

#### Frequency

Frequency

50 - 60 Hz

#### Use conditions

Operating temperature

-25 - 50 °C

Storage/transport temperature

-40 - 80 °C

#### Connection

Cross-section flexible conductor

1.5 - 4 mm<sup>2</sup>

Cross-section rigid conductor

2.5 - 6 mm<sup>2</sup>

#### Safety

Ingress Protection (IP) class

IP20

#### Electric current

Max. intensity of primary

480 A

Max. intensity of secondary

5 A

#### Sustainability

REACH-SVHC free

Yes

RoHS conform

Yes