



REU044X



Call push-button with LED name plate 4/1 built-in 2-wire one

Technical Features

Dimensions

Dimensions	85 x 85 mm
Height	85 mm
Width	85 mm

Voltage

Operating voltage	24 - 24 V
-------------------	-----------

Compatibility

Installation technique for door communication	IP
---	----

Controls and indicators

Closing time call button	3 s
Number of call buttons	4

Functions

Function	Ringling
----------	----------

Settings

Number of users	4
-----------------	---

Use conditions

Operating temperature	-20 - 55 °C
Storage/transport temperature	-30 - 80 °C

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes