



SVN311

Impulse 1NO Pushbutton

Technical Features

Equipment

| | |
|------------------------|----|
| Number of INV contacts | 0 |
| Number of NC contacts | 0 |
| Number of NO contacts | 1 |
| With signal lamp | No |

Electric current

| | |
|---------------------------|------|
| Momentary contact current | 16 A |
| Rated current | 16 A |

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Dimensions

| | |
|--------|----------|
| Height | 83 mm |
| Width | 17.50 mm |
| Depth | 66 mm |

Voltage

| | |
|---------------------------------|-------------|
| Rated insulation voltage U_i | 250 V |
| Rated operational voltage U_e | 230 - 230 V |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |

Illustrations | Drawings

