



WRPS12BSW

#### 10AX 1 Gang 2 Way Wall Switch Brushed Steel White Insert

##### Technical Features

###### Electric current

Switching current	10 A
-------------------	------

###### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

###### Voltage

Rated voltage	250 V
---------------	-------

##### Materials

Colour	Stainless steel
--------	-----------------

Surface finish	Matt
----------------	------

Material	Stainless steel
----------	-----------------

Treatment	Brushed
-----------	---------

##### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Controls and indicators

Number of buttons	1
-------------------	---

##### Dimensions

Dimensions	86 x 86 mm
------------	------------

Built-in depth	12 mm
----------------	-------

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Architecture

Control/operation element	Single rocker
---------------------------	---------------

##### Electric current

Rated current	10 A
---------------	------

##### Texts

Installation mode	For flush-mounted and hollow wall mounting
-------------------	--

Lighting	Without lighting (cannot be illuminated)
----------	--

Switch mode	2-way
-------------	-------

##### Sustainability

Halogen free	Yes
--------------	-----

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----