



VYGMS8W

**Group Metering Encl SA, 8, Wired**

**Technical Features**

**Installation, mounting**

Mounting on	DIN rail Surface mounting
-------------	------------------------------

**Electric current**

Rated current	100 A
Breaking and opening capacity I <sub>dm</sub>	25 kA

**Equipment**

Has mounting plate	No
Equipped with switch	MCCB
Number of switches	1
Type of busbar chassis	No chassis

**Capacity**

Number of modules	22
-------------------	----

**Dimensions**

Height	1350 mm
Width	625 mm
Depth	360 mm

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Materials**

Material	Steel
RAL code	7035
Colour	Light grey

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP23
Locking type	3-point lever

**Architecture**

Number of poles	22
-----------------	----